




How to print and measure

1. Confirm the 50 mm square and the 2.00 in bar with a real ruler. If either is short, reprint — the printer scaled.
 2. Cut the dashed strip. Fold the grey tab so its inner edge is your zero. Wrap just above the wrist bone — snug, not crushing.
 3. Read millimetres where the tab meets the scale (write mm; 165 mm $\approx$ 6.5"). Morning and after a warm afternoon — Singapore humidity swells wrists.
 4. Type that mm number into the fit checker with a published lug-to-lug. Missing L2L stays Incomplete — we do not invent tip-to-tip from Ø.
- Next page: illustrative silhouettes, not a named-brand try-on. Soft SGD on the site are planning labels, not quotes. A ten-minute try-on still wins.

Fit checker <https://wristfitsg.com/guides/fit-checker.html>

Sizing guide <https://wristfitsg.com/guides/sizing.html>

1 Cut

Dashed outline. Fold the grey tab to zero.


2 Wrap

Above the bone. Snug, not crushing. Read mm.

3 Type

Fit checker + published L2L. Try-on still wins.

Cut this strip · 0–240 mm · inches on the lower edge · gold band = 6–7" (site focus)



WristFit SG


Watch silhouettes at 1:1

A4 portrait · illustrative geometry — not a specific brand try-on

<https://wristfitsg.com/guides/paper-tape.html>


Two common small-wrist reference shapes, drawn at true size. Hold the sheet over your wrist (L2L runs along the forearm) or cut the outlines. Compare overhang to the green/red bar — that bar is the fit-checker span at ~6.5" ($165 \text{ mm} \div \pi \times 0.92 \approx 48.3 \text{ mm}$), not your measured wrist width.

L2L 44 mm
Ø36 / L2L ~44 mm — short-lug class (illustrative)



48.3 mm heuristic span — sits inside the ~6.5" span

L2L 50 mm
Ø39 / L2L ~50 mm — longer-lug class (illustrative)




48.3 mm heuristic span — overhangs the ~6.5" span

Same lesson as the site: diameter alone lies

A 36 mm short-lug shape (~44 mm tip-to-tip) typically stays inside a ~6.5" usable span. A 39 mm longer-lug shape (~50 mm) overhangs that same span.

These outlines are teaching geometry — not BB54, not OP36, not a boutique tray. Published L2L on the exact reference still has to be typed into the fit checker.

Next: <https://wristfitsg.com/guides/fit-checker.html> · <https://wristfitsg.com/guides/sizing.html> · try on in Singapore when you can. Soft SGD bands are planning labels, never a quote.



How to print and measure

1. Confirm the 50 mm square and the 2.00 in bar with a real ruler. If either is short, reprint — the printer scaled.
 2. Cut the dashed strip. Fold the grey tab so its inner edge is your zero. Wrap just above the wrist bone — snug, not crushing.
 3. Read millimetres where the tab meets the scale (write mm; 165 mm $\approx$ 6.5"). Morning and after a warm afternoon — Singapore humidity swells wrists.
 4. Type that mm number into the fit checker with a published lug-to-lug. Missing L2L stays Incomplete — we do not invent tip-to-tip from Ø.
- Next page: illustrative silhouettes, not a named-brand try-on. Soft SGD on the site are planning labels, not quotes. A ten-minute try-on still wins.

Fit checker <https://wristfitsg.com/guides/fit-checker.html>

Sizing guide <https://wristfitsg.com/guides/sizing.html>

1 Cut

Dashed outline. Fold the grey tab to zero.


2 Wrap

Above the bone. Snug, not crushing. Read mm.

3 Type

Fit checker + published L2L. Try-on still wins.

Cut this strip · 0–240 mm · inches on the lower edge · gold band = 6–7" (site focus)



WristFit SG


Watch silhouettes at 1:1

US Letter portrait · illustrative geometry — not a specific brand try-on

<https://wristfitsg.com/guides/paper-tape.html>


Two common small-wrist reference shapes, drawn at true size. Hold the sheet over your wrist (L2L runs along the forearm) or cut the outlines. Compare overhang to the green/red bar — that bar is the fit-checker span at ~6.5" ($165 \text{ mm} \div \pi \times 0.92 \approx 48.3 \text{ mm}$), not your measured wrist width.

L2L 44 mm
Ø36 / L2L ~44 mm — short-lug class (illustrative)



48.3 mm heuristic span — sits inside the ~6.5" span

L2L 50 mm
Ø39 / L2L ~50 mm — longer-lug class (illustrative)



48.3 mm heuristic span — overhangs the ~6.5" span

Same lesson as the site: diameter alone lies

A 36 mm short-lug shape (~44 mm tip-to-tip) typically stays inside a ~6.5" usable span. A 39 mm longer-lug shape (~50 mm) overhangs that same span.

These outlines are teaching geometry — not BB54, not OP36, not a boutique tray. Published L2L on the exact reference still has to be typed into the fit checker.

Next: <https://wristfitsg.com/guides/fit-checker.html> · <https://wristfitsg.com/guides/sizing.html> · try on in Singapore when you can. Soft SGD bands are planning labels, never a quote.